

BAE Bladder Accumulators

For working pressures up to 330 bar

Catalogue HY07-1235/UK February 2004



Bladder Accumulators Series BAE

Bladder Accumulators

Liquids are practically incompressible and therefore cannot be used directly for storing energy. Hydro-pneumatic accumulators use the differing compressibility of liquid and gaseous media to enable energy to be stored in liquids under pressure.

Parker's hydro-pneumatic bladder accumulators provide a means of regulating the performance of a hydraulic system. Their simple, compact, design ensures dependable performance, maximum efficiency and long service life.

Why use a Bladder Accumulator?

- stores energy under pressure
- damps out pump pulsation and flow fluctuations
- improves system efficiency
- supplements pump delivery
- supplies power in emergency
- absorbs hydraulic shocks
- compensates for pressure changes in cases of thermal stress
- very contaminant tolerant
- suitable for use with low-lubricity fluids
- fast response times
- Safety cannot disassemble under pressure

Technical Data

Standard volumes 1 – 50 litres

Operating pressure Up to 330 bar, with $p_2 < 4 \times p_1$

where p_1 = minimum working pressure and p_2 = maximum working pressure

Precharge pressure

- energy storage
- pulsation dampening
- shock suppression
90% of minimum working pressure
60% of maximum working pressure
60% of maximum pump pressure

Std. temperature range Shell and ports: -40°C to +80°C

Bladder and seals: -15°C to +80°C For use at other temperatures, please

consult factory.

Fluid type Mineral oil (standard compounds)

Flow Rate The maximum values listed in the selection table only apply in the case of vertical installation (fluid port facing downwards).

Positioning From vertical (fluid port downwards) to horizontal. Note that a minimum clearance of 200mm must be left above the gas valve for mounting the charging and gauging assembly – see page 5.

Contents	Page	Index	Page
Technical Data	2	Approvals	3
Design Features and Benefits	3	Bladder Compounds	5
Models, Capacities and Dimensions	3	Charging and Gauging Assemblies	5
Repair Kits and Parts List	4	Dimensions	3
Bladder Compounds	5	Features and Benefits	3
Charging and Gauging Assemblies	5	Flow Rates	3
Fluid Port Adapters	5	Fluid Port Adapters	5
Mounting Accessories	6	Model Numbers	7
How to Order	7	Mounting Accessories	6
		Ordering	7
		Parts List	4
		Repair Kits	4
		Technical Data	2

Parker Hannifin Corporation . . .

is a world leader in the manufacture of components and systems for motion control. Parker has more than 800 product lines for hydraulic, pneumatic and electro-mechanical applications in some 1200 industrial and aerospace markets. With over 45,000 employees and some 210 manufacturing plants and administrative offices around the world, Parker provides its customers with technical excellence and first class customer service. Parker Hannifin's Cylinder Division is

the world's largest supplier of hydraulic actuators and accumulators for industrial applications.

Catalogues describing our standard products are available from your nearest Parker sales office – please see the rear cover of this catalogue for addresses. Where an application demands a non-standard approach, special products can be designed to order – our engineers will be pleased to advise.



Features and Dimensions

Design Features and Benefits

1 Approvals

Parker's BAE bladder accumulators are built to meet the requirements of the European Pressure Directive (PED) 97/23/EC. Bladder accumulators are marked with the CE logo and supplied with a declaration of conformity. Hydraulic accumulators fulfil the safety requirements for all member states of the European Union, as well as Iceland, Liechtenstein, Norway and Switzerland.

2 Shell

Parker's bladder accumulator shells are made from seamless chrome-molybdenum alloy steel with forged ends, for maximum strength. The standard shell is suitable for use at operating temperatures down to -40°C.

3 Bladder


The absence of dynamic sealing surfaces makes bladder accumulators tolerant of contamination and particularly suitable for low-lubricity fluids. Specially formulated for low permeability, Parker's bladders retain their high performance under a wide range of operating conditions including closed loop operation. Optional bladder compounds are available to suit all common fluids and operating temperatures.

4 Gas Valve

Accurate precharging of a bladder accumulator is the key to long and reliable service life. All Parker's bladder accumulators feature a robust gas valve, which is readily accessible for maintenance purposes. A charging and gauging assembly, described on page 5, allows precharging and monitoring to be carried out quickly and easily.

5 Fluids and Fluid Ports

Parker's bladder accumulators are supplied as standard for use with hydraulic mineral oil. They are also available for use with other media, such as bio-degradable hydraulic fluids, non-inflammable liquids, emulsions, etc. Fluid ports are made from high-strength alloy steel, for maximum durability. BSPP ports are fitted as standard. Other port styles are available.



Models, Capacities and Dimensions

Model	Volume Litres	Mass Kg	Max flow I/min ¹
BAE01	1	5	240
BAE02	2.4	10	450
BAE04	3.7	13.5	450
BAE06	6.0	17.8	450
BAE10	9.2	29.5	900
BAE20	17.8	46	900
BAE24	22.5	53	900
BAE32	34.6	73	900
BAE50	50	101	900

	A max	B max	C max	ØD	Ød	F	ØG	ØH	SW
Ī	305	50	55	115	36	G ³ / ₄	35	51	32
Ī	535	67	55	115	36	G1 ¹ / ₄	53	75	50
	417	67	55	170	36	G1 ¹ / ₄	53	75	50
	540	67	55	170	36	G1 ¹ / ₄	53	75	50
	559	93	51	223	36	G2	76	101	73
	874	93	51	223	36	G2	76	101	73
	1009	93	51	223	36	G2	76	101	73
	1394	93	51	223	36	G2	76	101	73
	1938	93	85	223	75	G2	76	101	73

J	K
G³/8	8
G ³ / ₄	10
G ³ / ₄	10
G ³ / ₄	10
G1	13

Notes


All dimensions are subject to manufacturing tolerances. All dimensions are in millimetres unless otherwise stated.

In line with our policy of continuing product improvement, specifications in this catalogue are subject to change without notice.



¹ A minimum liquid volume (10% of V₀) must be maintained inside the accumulator


Spare Parts and Repair Kits



Gas Valve Assembly

Parts List (All Models)

- 1* Protective cap
- 2* O-ring protective cap
- 3* Gas valve
- 4* Gas valve lock nut
- 5* Bladder
- 6 Shell
- 7 Identification plate
- 8 Hydraulic port assembly
- 9* Anti-extrusion ring moulding
- 10 Port spacer
- 11* O-ring hydraulic port
- 12* O-ring back-up washer
- 13 Fluid port lock nut
- 14* Bleed plug
- 15* Sealing washer for bleed plug
- * included in repair kit



Fluid Port Assembly - All Models

Repair Kits

Repair kits are available for all accumulator models. When ordering repair kits, please supply the complete model number from the identification plate and specify the fluid type and the temperature at which the accumulator is to be used. The repair kit comprises those parts marked with an asterisk in the parts list. For a full description of the compound abbreviations, see 'Bladder Compounds' on page 5.

		Compound						
Model	NBR	IIR	FPM	EPDM	ECO			
BAE01	BAE-BK01NBR							
BAE02	BAE-BK02NBR							
BAE04	BAE-BK04NBR							
BAE06	BAE-BK06NBR							
BAE10	BAE-BK10NBR		Consult	Factory				
BAE20	BAE-BK20NBR							
BAE24	BAE-BK24NBR							
BAE32	BAE-BK32NBR							
BAE50	BAE-BK50NBR							



Bladder Compounds

Parker offers bladders moulded from a variety of compounds, to suit a wide range of fluids and operating temperatures. Unless ordered specially, a Group 1 (nitrile) bladder will be supplied. The table lists the compounds in which bladders are available, their recommended operating temperature ranges,

and the types of fluids with which the different materials are generally compatible. Note that temperature ranges may vary depending on the fluid used in the hydraulic system. If in doubt, contact the factory with details of the application.

Group	Bladder Compound	Fluid Medium	Temperature Range
		General purpose, mineral oil-based fluids	-15°C to +80°C
1	Nitrile (NBR)	HFA and HFB fluids ¹	+5°C to + 55°C
		HFC fluids ¹	-15°C to +60°C
2	Low Temperature Nitrile (LT NBR)	Mineral oil-based fluids	-35°C to +75 °C
3	Butyl (IIR)	Most phosphate ester and some synthetic fluids	-15°C to +80°C
5	Fluorocarbon Elastomer (FPM)	High temperature and/or synthetic fluids	-20°C to +100°C ²
7	Ethylene Propylene Diene (EPDM)	Phosphate ester-based fluids and water	-40°C to +80°C ³
9	Epichlorohydrine (ECO)	General purpose fluids with enhanced low temperature performance	-32°C to +80°C ³

¹ Check with fluid supplier that fluid is compatible with nitrile compounds

Port Sizes

Fluid ports are made from high-strength alloy steel, for maximum durability. BSPP ports are fitted as standard. ISO 6149 and SAE ports are available on request.

Model	BSPP	ISO 6149-1	SAE	-Thread	SAE Flange (ISO 6162)
BAE01	G ³ / ₄	M27x2	#12	1 ¹ / ₁₆ "-12	n/a
BAE02 - BAE06	G1 ¹ / ₄	M42x2	#20	1 ⁵ / ₈ "-12	1" 6000 psi Code 62
BAE10 - BAE50	G2	M60x2	#24	1 ⁷ / ₈ "-12	1 ¹ / ₂ " 6000 psi Code 62

Fluid Port Adapters

A range of adapters is available for use with Parker's bladder accumulators, to reduce the size of the fluid port. Adapters are supplied complete with a nitrile O-ring.

Model	Fluid Port Thread	Adapter Thread	Part No.
BAE01	G ³ / ₄	G ³ / ₈	BPA1
BAE02 - BAE06	G1 ¹ / ₄	G ³ / ₄	BPA2
BAE10 - BAE50	G2	G1	BPA3

Charging and Gauging Assembly

The charging and gauging assembly enables the user to charge Parker's bladder accumulators with nitrogen, and to test and alter the precharge pressure. It attaches to the accumulator's gas valve, and can be connected by hose to a standard commercial nitrogen bottle. Each kit contains:

- Test and filling apparatus incorporating gas valve key and bleed valve
- Filling hose, length 2.5m
- Protective case
- Gas valve adapters to fit all standard bladder accumulators
- 25 bar and 250 bar pressure gauges

Parker strongly recommends that the nitrogen bottle used should be fitted with a high pressure regulator.

Charging and Gauging Assembly with Adapter – All Models				
Territory	Gas Bottle Fitting	Part No.		
UK	5/8 BSP (male)	UCA 02		
France	W 21.7 x 1/14" (female)	UCA 04		
Germany	W 24.32 x 1/14" (female)	UCA 01		
Italy	W 21.7 x 1/14" (male)	UCA 05		
US	0,960 x 1/14" (male)	UCA 03		




² For operating temperatures above 80°C, please consult the factory


³ For operating temperatures below -20°C, please consult the factory


Accessories


Mounting Accessories

Parker clamp and base brackets provide a simple and secure method of mounting the accumulator. The clamps and brackets are galvanised to resist damage from corrosion. Rubber inserts absorb vibration and resist deformation in high temperature environments.









1 litre

2.5 - 6 litres

10 - 24 litres

32 - 50 litres

Clamp Bracket Assembly

Model	Nominal Volume (I)	Part No.	Quantity	See Figure
BAE01	1	CB1	1	1
BAE02	2.5	CBI		l
BAE04	4	CB2	2	
BAE06	6	CBZ		2
BAE10	10			
BAE20	20		1	
BAE24	24	CB3		3
BAE32	32		2	
BAE50	50			

А	В	С	ØD	E	Н	К	ØL	М
138	100	159	114	-	73	30	9	14
188	148	181	168	230	92	40	9	14
270	216	241	226	290	123	40	15	21




Fig. 1




Fig. 2





Fig. 3




Base Bracket Assembly

Model	Nominal Volume (I)	Part No.
BAE10 - BAE50	10 - 50	BB1

А	В	С	D	Е	F	G	Н	К	L
123	235	100	170	200	30	260	25	115	17






All dimensions are in mm unless otherwise stated



Bladder Accumulators Series BAE

How to Order Bladder Accumulators



BAE Series bladder accumulators are supplied with a Declaration of Confirmity in accordance with European Pressure Equipment Directive 97/23/EC, and with an operating manual and a drawing showing the main dimensions and materials.



Hydraulics Group Sales Offices

Europe

Austria

Wiener Neustadt Tel: +43 (0)2622 23501 970 Fax: +43 (0)2622 23501 977

Belgium Nivelles

Parc Industriel Sud-Zone II
Tel: +32 (0)67 280 900
Fax: +32 (0)67 280 999

Czech Republic

Tel: +420 2 830 85 221 Fax: +420 2 830 85 360

Denmark

Tel: +45 4356 0400 Fax: +45 4373 8431

Finland

Tel: +358 (0)9 4767 31 Fax: +358 (0)9 4767 3200

France

Contamine-sur-ArveTel: +33 (0)450 25 80 25
Fax: +33 (0)450 03 67 37

Germany

Kaarst Tel: +49 (0)2131 4016 0 Fax: +49 (0)2131 4016 9199

Hungary

Tel: +36 (06)1 220 4155 Fax: +36 (06)1 422 1525

Ireland

Tel: +353 (0)1 801 4010 Fax: +353 (0)1 801 4132

Corsico (MI) Tel: +39 02 45 19 21 Fax: +39 02 4 47 93 40

The Netherlands Oldenzaal

Tel: +31 (0)541 585000 Fax: +31 (0)541 585459

Ski

Tel: +47 64 91 10 00 Fax: +47 64 91 10 90

Warsaw

Tel: +48 (0)22 863 49 42 Fax: +48 (0)22 863 49 44

Portugal Leca da Palmeira Tel: +351 22 9997 360 Fax: +351 22 9961 527

Slovakia Ref. Czech Republic

Spain

Tel: +34 91 675 73 00 Fax: +34 91 675 77 11

Sweden

Spånga Tel: +46 (0)8 597 950 00 Fax: +46 (0)8 597 951 10

United Kingdom Watford (industrial)

Tel: +44 (0)1923 492 000 Fax: +44 (0)1923 256 059

Ossett (mobile)
Tel: +44 (0)1924 282 200 Fax: +44 (0)1924 282 299

International

Australia

Castle HillTel: +61 (0)2-9634 7777
Fax: +61 (0)2-9899 6184

*Milton, Ontario*Tel: +1 905-693-3000 Fax: +1 905-876-0788

BeijingTel: +86 10 6561 0520 Fax: +86 10 6561 0526

Asia Pacific Group

Hong Kong, Kowloon Tel: +852 2428 8008 Fax: +852 2425 6896

Mumbai

Tel: +91 22 7907081 Fax: +91 22 7907080

Tokyo Tel: +(81) 3 6408 3900 Fax: +(81) 3 5449 7201

Latin America Group Brazil

Tel: +55 12 3954-5100 Fax: +55 12 3954-5266

South Africa Kempton Park

Tel: +27 (0)11-392 7280 Fax: +27 (0)11-392 7213

Cleveland (industrial)

Tel: +1 216-896-3000 Fax: +1 216-896-4031 Lincolnshire (mobile) Tel: +1 847-821-1500 Fax: +1 847-821-7600

Parker Hannifin is the world's premier supplier of motion and control systems and solutions, with sales and manufacturing facilities throughout the world. For product information and details of your nearest Parker sales office, visit us at www.parker.com or call free on 00800 2727 5374.



Catalogue HY07-1235/3-UK 2M 02/04 PD

© Copyright 2004 Parker Hannifin Corporation All rights reserved.